






Quick Start for the HOBO® MX Temp/RH Logger (MX1101)

- 1**
 - Download HOBOnnect® to a phone or tablet from the App Store® or Google Play™.
 - Download HOBOnnect to a Windows® computer from www.onsetcomp.com/products/software/hobonnect.
- 2** Install the batteries in the logger. Open the battery door on the back of the logger and insert two AAA batteries observing polarity. Reinsert the battery door and snap it back into place.
- 3** Open the app. Enable Bluetooth® in your device settings if prompted.
- 4** Tap Devices in the app. Tap the logger in the app to connect to it. If the logger does not appear, make sure it is within range of your phone, tablet, or computer.
- 5** Tap  to set up the logger. Choose your logger settings and then tap  to save the settings to the logger.
- 6** The logger will begin logging data based on the settings you selected in the app. Press the start button on the logger if you set it up to start logging with a button push. Deploy the logger using the magnets on the back of the logger case or the mounting materials included.
- 7** To offload data from the logger to your device, tap Devices. Connect to the logger and tap . To view or export the data, tap HOBO Files, tap  (if applicable), and tap .



For detailed specifications and information about the logger, scan the code at left or go to www.onsetcomp.com/support/manuals/17840-mx1101-manual.



1-508-759-9500 (U.S. and International)
1-800-LOGGERS (564-4377) (U.S. only)
www.onsetcomp.com/support/contact

© 2014–2021 Onset Computer Corporation. All rights reserved. Onset, HOBO, and HOBOnnect are registered trademarks of Onset Computer Corporation. App Store is a service mark of Apple Inc. Google Play is a trademark of Google LLC. Windows is a registered trademark of Microsoft Corporation. Bluetooth is a registered trademark of Bluetooth SIG, Inc. All other trademarks are the property of their respective companies.

This product has been manufactured by Onset Computer Corporation and in compliance with Onset's ISO 9001:2015 Quality Management System.

Patent #: 8,860,569

17839-L MAN-QSG-MX1101